

## **TECHNICAL DATA SHEET**



Scan Here For More Info

# Res-protek 8104

# Ammonia Methylamine Gas & Vapour Twin Filter - K<sub>1</sub>

#### **Product Introduction:**

UDYOGI | Res-protek 8104 Filter is an K1 twin filter designed to protect against certain ammonia methylamine gases and vapors.

Featuring a bayonet connector, it integrates seamlessly with Res-protek half masks and full-face masks.

#### **Features:**

- Protection: Provides effective filtration against certain ammonia methylamine gases and vapors.
- Combined Protection: For additional protection against particulates, use the 8104 filter with the 811 pre-filter and 810 retainer on a Res-protek face mask. This setup covers gases, vapours, and particulates.
- Bayonet Connector: Features a bayonet connector for secure and easy attachment to Res-protek half masks and full-face masks.
- Swept-Back Design: The swept-back design enhances the field of view and comfort for the wearer.
- Enhanced Comfort: Designed for improved comfort and usability, ensuring a better fit and extended wear.
- Optimized Shape: The filter's ergonomic shape ensures a snug fit within respiratory masks, improving overall safety and user comfort.
- Low Maintenance: Designed to require minimal upkeep, reducing the frequency of filter changes and associated maintenance efforts.

#### **Compatibility:**

 The 8104 twin filters are compatible with Res-Protek's half and full-face masks offering flexibility across different work environments

#### **Standard:**

As per EN 14387:2004+A1:2008

# **Product Specifications:**

Model: 8104
Filter Class: 1
Filter Type: K
Colour Code: Green
Type of PPE Category: III

**Type of Device:** Gas & Vapour Filter **PPM:** up to 1000ppm

Connection Type: Bayonet
Designated to be Used: Twin Filter
Reusability: Multiple Uses

Packing Per Pouch: 1 pair
Packing Per Case: 30 pairs

#### **Benefits:**

- Wide Range of Applications: Suitable for various industrial settings, which helps reduce inventory needs.
- Cost Savings: Reusable design reduces the need for frequent replacements, cutting costs.
- Quick and Easy Replacement: Bayonet connection allows swift filter changes with effortless attachment and removal, minimizing downtime.
- Simple Installation: Quick and straightforward installation process that minimizes training requirements.

Udyogi

E-mail: <u>info@udyogi.net</u>
Website: <u>www.udyogisafety.com</u>







### 8104 Ammonia, Methylamine Gas & Vapour Filter

#### Scan Here For More Info

#### **Application:**

8104 Filter is essential for work environments where protection against certain ammonia, methylamine gas and vapour is required, including

- Pharmaceutical Processing & Manufacturing.
- Chemical Processing/Handling/Clean-Up.
- General Maintenance, Cleaning, Renovation.
- General Industrial Operations & Settings.
- Pesticides, Agrochemicals Handling.
- Sealants Processing/Handling.
- Assembly Operations.

- Cleaning and Degreasing Processes.
- Laboratories Operations.
- Adhesives Processing/Handling.
- Food Processing.
- Adhesives Processing/Handling.
- Refrigeration Systems (heating, ventilation, and air conditioning).

### Industry:





Chemical



Automobile







Transportation





Pharmaceutical











Steel



Paper

General Manufacturing

Oil & Gas

Construction

Manufacturing

Agriculture

Textile

**FMCG** 


#### **Usage Instructions:**

Install the Filters:

Match the filter's plastic connection with the filter holder on the face mask. Press and turn the filter clockwise until it is securely locked in place.

Repeat the process for the second filter.

- Verify Seal: Confirm that both filters are properly seated and that there are no gaps around the connections.
- Regular Inspection: Periodically check the filters for signs of damage, clogging, or reduced airflow.
- Replace When Necessary: Replace the filters if they become clogged, damaged, or if breathing resistance increases significantly.
- Dispose Properly: Follow local regulations for the disposal of used filters and respiratory components.





#### Storage:

- Keep in a Cool, Dry Place: Store the filter in a fresh, cool, and dry environment.
- **Avoid Direct Sunlight:** Keep the filter away from direct sunlight to prevent degradation.
- **Temperature Limit:** Do not expose the filter to temperatures exceeding 50°C or direct sunlight.
- Humidity Control: Store in an environment with low humidity, ideally not exceeding 80% relative humidity.
- Avoid High Heat Sources: Keep away from high heat sources to maintain filter integrity.

Warning: These filters do not supply oxygen. Do not use in atmospheres containing less than 19.5% oxygen. Caution must be given in oxygen-enriched atmospheres (ignition), and it is prohibited to enter explosive atmospheres (e.g., through solvents). Filters should not be used in firefighting or to work with open flames or molten metal since.

Before use, the wearer must read and understand the User Instructions provided as a part of the product packaging.

Udyogi