



Scan Here For More Info

TECHNICAL DATA SHEET

Res-protek **485**

Filter Retainer for Pre-filter 4N11

Product Introduction:

UDYOGI | Res-protek 485 Filter Retainer is designed to securely hold 4N11 particulate filters in place within res-protek 4000 series single filters. Its robust design ensures the proper alignment and stability of particulate filters.

Features:

- **Secure Filter Holding:** Designed to provide a firm grip on filters, preventing displacement and ensuring consistent filtration performance.
- **High Durability:** Made from polyethylene to withstand demanding conditions and ensure long-term reliability.
- **Versatile Compatibility:** Suitable for a wide range of res-protek filters, making it adaptable to different filtration systems.
- **User-Friendly Installation:** Features a straightforward design that allows for easy installation and removal, facilitating maintenance and replacement.
- **Corrosion and Chemical Resistant:** Constructed to resist corrosion and damage from chemicals, extending its service life.

Benefits:

- **Enhanced Filtration Efficiency:** Ensures filters are properly positioned.
- **Reduced Maintenance Costs:** Simplifies the installation and replacement process, reducing labor costs and downtime associated with filter maintenance.

Maintenance:

Regularly inspect the filter retainer for signs of damage. Clean periodically to ensure optimal performance and replace as needed.

Cleaning and Disinfection:

- **Filter Removal:** Remove filters before cleaning the retainer.
- **Cleaning Process:** Clean the retainer with a wet cloth and immerse it in a warm water solution (not exceeding 50°C) using a neutral detergent if necessary.
- **Avoid Harsh Chemicals:** Do not clean with solvents, strong detergents, or petroleum-based products.



Product Specifications:

| | |
|--------------------------|-----------------|
| Model : | 485 |
| Colour: | Grey |
| Type of Device: | Filter Retainer |
| Construction: | Polyethylene |
| Packing Per Box: | 10 pcs |
| Packing Per Case: | 100 pcs |

Usage Instructions:

485 It must be used as a filter retainer with the Res-protek 4N11 pre-filter along with 4000 series filters.

Assembly Instructions:

- **Insert the Pre-Filter:** Place the 4N11 pre-filter into the 485 filter retainer with the printed side of the filter facing up. Press the filter into the retainer until it is securely attached to the filter.
- **Ensure Full Coverage:** The 4N11 pre-filter must completely cover the face of the filter.



Storage:

- **Keep in a Cool, Dry Place:** Store the filter in a fresh, cool, and dry environment.
- **Avoid Direct Sunlight:** Keep the filter away from direct sunlight to prevent degradation.
- **Avoid High Heat Sources:** Keep away from high heat sources to maintain filter integrity.